


# Café Purist

The ultimate water recipe for coffee



*Caware*  
Water Filter Solutions



**Caware Filtering Corporation**

No.123, Ta-Jing 1<sup>st</sup> St. Ren Wu, Kaohsiung, Taiwan

[www.caware.com.tw/cafePurist](http://www.caware.com.tw/cafePurist)

[caware@caware.com.tw](mailto:caware@caware.com.tw)



# Café Purist

## *Crema Formula*

Caware's Advanced Technology contains multiple filtration stages inside cartridges. Effectively water softening and rich Mg2+ leaching. Effectively boost up brewing reaction and condense brewing efficiency.

The composition of a cup of café is around 98-99% water. To customize the ingredient of water by Caware Water Recipe shall help optimize the aroma taste of every cup of café. The decisive factor affects the taste or aroma of café is reaction of water with 6-7 main acid of café bean during brewing process.

## *Shots Formula*

Caware's Advanced Technology contains multiple filtration stages inside cartridges. This longevity design is superior on water softening for large water consuming demand.





# Products & Specifications

## Single Cartridge




Claiming	Well-Balanced of Mg2+ Water Softening Chemical Reduction Particle Reduction
Cartridge size	3.7"OD x 14"L ( 94mm x 356mm) 5.4"OD x 17"L (136mm x 432mm)
Model No.	RM-14WM / RM-17BWM

## Manifold in Stages

It's easy and simple to connect two or more stages of filter cartridges to increase the capacity or achieve different claiming.



## Adapter head with By-Pass Valve



RecipeHead™

Model No.	#AH-P-WM+
Spec.	3/8" NPT male port with dual in-out check valve. 4 levels bypass valve.

# Products & Specifications

## Single Cartridge



Claiming	Well-Balanced of Mg2+ Water Softening Chemical Reduction Particle Reduction
Cartridge size	3.3"OD x 14"L (86mm x 350mm) 3.3"OD x 20"L (86mm x 512mm)
Model No.	RM-14EP+ / RM-20EP+

## Manifold in Stages

It's easy and simple to connect two or more stages of filter cartridges to increase the capacity or achieve different claiming.



## Adapter head with flow-meter



Flow Meter

Model No.	#AH-P-EP+-FM
Spec.	3/8" NPT female port with dual in-out check valve.

Adapter Head with flow-meter of compact design monitors the filter life usage.

# Products & Specifications

## Single Cartridge




Claiming	Longevity Life Span Water Softening Chemical Reduction Particle Reduction
Cartridge size	3.7"OD x 14"L ( 94mm x 356mm) 5.4"OD x 17"L (136mm x 432mm)
Model No.	RL-14WM / RL-17BWM

## Manifold in Stages

It's easy and simple to connect two or more stages of filter cartridges to increase the capacity or achieve different claiming.



## Adapter head with By-Pass Valve



RecipeHead™

Model No.	#AH-P-WM+
Spec.	3/8" NPT male port with dual in-out check valve. 4 levels bypass valve

# Products & Specifications

## Single Cartridge



Claiming	Longevity Life Span Water Softening Chemical Reduction Particle Reduction
Cartridge size	3.3"OD x 14"L (86mm x 350mm) 5.4"OD x 17"L (136mm x 432mm)
Model No.	RL-14EP+ / RL-20EP+

## Manifold in Stages

It's easy and simple to connect two or more stages of filter cartridges to increase the capacity or achieve different claiming.



## Adapter Head with Flow-Meter



Flow Meter

Model No.	#AH-P-EP+-FM
Spec.	3/8" NPT female port with dual in-out check valve.